

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		RELEASED PER ECO-10-009942	28MAY2010	DD	RB
B		REVISED PER ECO-13-019865	27DEC2013	DR	RB

D

C

B



A

D

C


B

A




SECTION A-A
OPEN POSITION


2098241-1 SHOWN
ORANGE TPA
KEY A



SECTION A-A
CLOSED POSITION




2098241-2
PURPLE TPA
KEY B
SCALE 2:1



2098241-3
BLUE TPA
KEY C
SCALE 2:1

- 1 HOUSING AND COVER MATERIAL: 25% GLASS FILLED THERMOPLASTIC; COLOR: NATURAL (BROWN)
- 2 TPA MATERIAL: 15% GLASS FILLED THERMOPLASTIC COLOR: (SEE TABLE)
- 3 SEAL MATERIAL: SILICONE COLOR: MARINE BLUE
- 4. RECOMMENDED WIRE DIAMETER RANGE IS 2.18-3.67 MM



SCALE 2:1

C	BLUE	2098241-3
B	PURPLE	2098241-2
A	ORANGE	2098241-1
KEY	TPA COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 05 JUN 2009 RUSTY WORTHINGTON	TE Connectivity			
DIMENSIONS: mm		CHK 05 JUN 2009 ROGER BALTER				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.5 2 PLC ±0.30 3 PLC ± 4 PLC ± ANGLES ± FINISH -		APVD 05 JUN 2009 ROGER BALTER	NAME CAP ASSEMBLY, 6 POSITION, DUAL ROW, AMPSEAL 16, VO MATERIAL			
MATERIAL		PRODUCT SPEC 108-2184	SIZE 114-13065		RESTRICTED TO -	
1 2 3		APPLICATION SPEC 114-13065	WEIGHT 15.5±1g		SCALE 3:1	
		CUSTOMER DRAWING	A200779		SHEET 1 OF 1	
			C-2098241		REV B	