Part Number : 1200698557
Product Description : M12 Signal, A-Coded, Single-Ended Cordset with Knurled Hexnut, 4 Poles, Female (Straight) to Pigtail, 22 AWG, Black Shielded TPU WSOR Cable, 15.0m (49.21') Length
Series Number : 120069
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : 804S00BS1M150



Documents and Resources

Drawings

1200698557_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	120069
Description	M12 Signal, A-Coded, Single-Ended Cordset with Knurled Hexnut, 4 Poles, Female (Straight) to Pigtail, 22 AWG, Black Shielded TPU WSOR Cable, 15.0m (49.21') Length
IP Rating	IP67
Product Name	M12 Signal,Micro-Change (M12)
Type	Single Ended
UPC	889056073776

Agency

UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V

Physical

Cable Diameter	5.70mm (.224")
Cable Length	15.0m (49.21')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded, Knurled Hexnut
Gender	Female-Pigtail
Keyway	A-Coded
LED Indicator	None

Downloaded from Arrow.com.

Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	728.228/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-40° to +90°C
Wire/Cable Type	UL 21215, WSOR
Wire Size (AWG)	22

Downloaded from Arrow.com.