

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2162881063

Status:

Active

Overview:

MX150 Connector System

Description:

MX150 Male-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Dual Row, 600.00mm Length, Tin (Sn) Plating, 6 Circuits, Black



Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Packaging Specification 2162801021-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	216288
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Single Ended Connector
Connector to Connector	MX150-to-Pigtail
Overmolded	No
Overview	MX150 Connector System
Product Name	MX150
Taxonomy	Power and Signal Cable Assembl
Type	Discrete Wire Assembly, Sealed Assembly
UPC	193264714766
Physical	
Cable Length	600.00mm
Circuits (Loaded)	6
Color - Resin	Black
Gender	Male-Pigtail
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	SPS/Nylon
Net Weight	1133.300/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	3.50mm
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.70mm max.
Wire Size AWG	14
Wire/Cable Type	TXL Stranded
Electrical	
Current - Maximum per Contact	22.0A
Voltage - Maximum	14V DC
Material Info	
Reference - Drawing Numbers	
Packaging Specification	2162801021-001
Sales Drawing	2162881061-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained per -
D(2022)9120-DC (17
Jan 2023)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China RoHS

Green Image

China ROHS

ELV

RoHS Phthalates

Not Relevant

Not Contained

Search Parts in this Series

216288 Series

Mates With

MX150 Sealed Dual Row Female Connector
33472

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION