Datasheet for part number DBM-17P2P-1A9N-A191-K87

Our Catalog Part Number: DBM-17P2P-1A9N-A191-K87
Our Global Manufacturing Part Number: 121551-1660
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: COMBO D

Product Datasheet	
General	Combo D Series: D-Subminiature offering mixed layouts
Wire Gauge Range AWG	AWG 8-26
Mating Cycles	200
Contact Arrangement	17P2 (15 contacts size 20, 2 contacts size 8)
Dielectric Withstanding Voltage	1000 VAC at sea level
Current Rating Signal Contacts	7.5 max
Current Rating Size 8 Contacts	40 A max
Contact Resistance	10 milli Ohm max
Operating Temperature	-55°/+125°
Salt Spray Test	20 hours
Shell Material	steel
Shell Finish	pure tin over nickel
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Gender	Pin
Contact Type	High Power
Contact Material	copper alloy
Contact Finish	gold over nickel (Performance Class 2)
Mounting Method	metal bracket and captive nut M3

Specifications and dimensions subject to change.

Downloaded from Arrow.com.