



Chloroprene tubing and grommets

- HS

- HT

For years, HellermannTyton tubing and grommets have been the engineer's preferred choice for electrical insulation and mechanical protection in a diverse range of electronic and electrical industries.

To save time and effort when fitting the tubing, try the HellermannTyton NA three pronged pliers (see Chapter 6.3) and the Hellerine lubricant (see end of Chapter), which are specially designed for use with HellermannTyton chloroprene tubing.

Features and Benefits

- Highly elastic Chloroprene tubing
- Easy to fit
- Very good insulating characteristics
- Available on reels



Chloroprene tubing.

MATERIAL	Chloroprene (CR)
Operating Temperature	-25 °C to +100 °C
Flammability	UL94 HB and FMVSS-302
Elongation at break	min. 400%

RoHS ✓



Chloroprene tubing


TYPE	Supplied Ø D min.	Wall (WT)	Bundle Ø max.	Reel Length	Colour	Article-No.
HS0	1.25	0.50	2.0	100 m	Black (BK)	608-00100
HS1	1.75	0.50	3.5	100 m	Black (BK)	608-00150
HS1K	2.50	0.90	4.0	100 m	Black (BK)	608-00200
HS2	3.00	0.60	6.0	100 m	Black (BK)	608-00250
HS2K	4.00	1.50	8.5	50 m	Black (BK)	608-00300
HS3	5.00	0.70	9.0	100 m	Black (BK)	608-00350
HS4	7.50	0.80	13.0	25 m	Black (BK)	608-00400
HS5	10.00	1.00	20.0	25 m	Black (BK)	608-00450
HS8	12.00	1.00	23.0	25 m	Black (BK)	608-00500
HS9	14.00	1.00	25.0	20 m	Black (BK)	608-00550
HS10	17.00	1.00	28.0	20 m	Black (BK)	608-00600

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.



Chloroprene tubing and grommets

- HT



Chloroprene tubing

TYPE	Supplied Ø D min.	Wall (WT)	Bundle Ø max.	Length (L)	Pack Cont.	Colour	Article-No.
HT0	1.25	0.50	2.0	20.0	1,000 pcs.	Black (BK)	600-10200
HT1	1.75	0.50	3.5	20.0	1,000 pcs.	Black (BK)	600-15200
HT1K	2.50	0.90	4.0	25.0	500 pcs.	Black (BK)	600-20250
HT2	3.00	0.60	6.0	25.0	500 pcs.	Black (BK)	600-25250
HT2K	4.00	1.50	8.0	30.0	500 pcs.	Black (BK)	600-30300
HT3	5.00	0.70	9.0	25.0	500 pcs.	Black (BK)	600-35250
HT4	7.50	0.80	13.0	30.0	200 pcs.	Black (BK)	600-40300
HT5	10.00	1.00	20.0	35.0	200 pcs.	Black (BK)	600-45350
HT8	12.00	1.00	23.0	50.0	100 pcs.	Black (BK)	600-50500
HT9	14.00	1.00	25.0	50.0	100 pcs.	Black (BK)	600-55500
HT10	17.00	1.00	28.0	50.0	100 pcs.	Black (BK)	600-60500

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.