



Dimensions in mm

Technical data	
Connection type	RJ-45 plug
Pole number	8
Cable connection direction to mating direction	0°
Communication/fieldbus	ETHERNET
Code	TIA-568A
Transmission rate	10000 Mbit/s

Connection data	
Connection type 1	IDC contact
Solid conductor	0.21 ... 0.32 mm² / 24/1 ... 22/1 AWG
Stranded conductor	0.11 ... 0.36 mm² / 27/7 ... 22/7 AWG



Physical data	
Width	13.8 mm
Height	16.2 mm
Depth	49 mm

Mechanical data	
Connection requirement (permissible cable type)	Cat. 6A
Connectable sheathed cable diameter	5.5 ... 9 mm
Housing material	Zinc die casting
Weight	18 g

Environmental requirements	
Ambient temperature (operation)	-40 ... +85 °C
Ambient temperature (storage)	-40 ... +85 °C
Protection type	IP20
Relative humidity (without condensation)	95 %
Fire load	0 MJ
Standards/specifications	IEC60603-7-51, ISO/IEC 11801, IEEE 802.3an EIA/TIA 568-C.2 DIN EN 50173-1 UL 1863 UL 2043

Commercial data	
PU (SPU)	1 pcs
Packaging type	Bag
Country of origin	TW
GTIN	4055143586184
Customs tariff number	85366990990

Product classification	
UNSPSC	39121413
eCl@ss 10.0	27-24-26-92
eCl@ss 9.0	27-24-26-92
ETIM 9.0	EC001121
ETIM 8.0	EC001121
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption



Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
UL Underwriters Laboratories Inc.	UL 1977	E345416

Downloads

Environmental Product Compliance

Compliance Search
Environmental Product Compliance 750-977/000-011

Documentation

Bid Text			
750-977/000-011	06.10.2017	doc 24.50 KB	
750-977/000-011	19.02.2019	xml 3.71 KB	

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com