

Representative Image

Catalog No. TC112-TB

Description: MINI MTG BASE .75X.37IN NAT NYL SCR

UPC No 786210822587

Home > Wire & Cable Management > Ty-Rap > Cable tie mounts

Miniature Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 19.1mm (0.75 Inches), Width of 9.5mm (0.374 Inches), Height of 4.8mm (0.189 Inches), Fillister-Head Screw Mounting Method

Descriptors

Category	Cable tie mounts
Special Features	These miniature mounting bases are ideal for high-density packaging. Threaded insert permits screw to come from outside of mounting surface.

Specifications

Cable Size	0.19 in , 4.82 mm
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

Classifications

Brand Name	Ty-Rap

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E49405	N/A	ZODZ	N/A	N/A

by ABB

Downloaded from Arrow.com.