



Part Number : [192030389](#)
Product Description : Krimptite Ring Tongue
Terminal for 12-10 AWG Wire, Stud Size 10
(M5)
Series Number : 19203
Status : Active
Product Category : Ring and Spade Terminals



Documents & Resources

Drawings
[192030389_sd.pdf](#)

Specifications
[PS-19902-011-001.pdf](#)
[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19203
Description	Krimptite Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5)
Keyword	Ring Terminal, Ring Terminals
Product Name	Krimptite
Type	Ring
UPC	822348424788

Agency

UL	E32244
----	--------

Physical

Barrel Type	Closed
Insulation	None
Material - Metal	Steel
Material - Plating Mating	Nickel
Net Weight	1.180/g
Packaging Type	Carton
Stud Size	10 (M5)
Temperature Range - Operating	483°C
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	5.70mm max.
Wire Size (AWG)	10, 12
Wire Size mm ²	4.00-6.00

Application Tooling

Global

Description	Part Number
-------------	-------------

PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm ² - 0.5mm ²	<u>640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>640160038</u>

This document was generated on Mar 12, 2025