

Application Tooling > Applicators

OC-AT-S-FM-620O100O-752-091-1274



✓ ACTIVE

AMP

TE Part # **2837236-1**
TE Internal #: **2837236-1**

Feed Type : **Mechanical**
Applicator Style : **OCEAN**
Application Interface : **Male Adapter Post - Atlantic Style**
Service Options : **Capability Study, Crimped Samples, Cross Section - Photograph**
Terminator Type : **30 mm (1.12") Stroke Terminator, 40 mm (1.62") Stroke Terminator**

 Add to List ▼

 Similar Products

Compatible Parts & Tooling

SHOP OUR DISTRIBUTORS

No distributor is reporting inventory. For additional information, [contact us](#)

We are here to help!

Get in touch with our product experts.

CHAT WITH US

EMAIL US

CALL US

DOCUMENTS	FEATURES	PRODUCT COMPLIANCE
Product Drawings	Customer Accessible Production Drawing OC-AT-S-FM-620O100O-752-091-1274  OC-AT-S-FM-620O100O-752-091-1274 English	
Datasheets & Catalog Pages	 ENG_DS_1-1773864-9_0618.pdf English	
Instruction Sheets	Instruction Sheet (U.S.)  ENG_SS_408-8059_G.pdf English	
Please review product documents or contact us for the latest agency approval information.		
Other	Feed Type : Mechanical Applicator Style : OCEAN Application Interface : Male Adapter Post - Atlantic Style Service Options : Capability Study, Crimped Samples, Cross Section - Photograph Terminator Type : 30 mm (1.12") Stroke Terminator, 40 mm (1.62") Stroke Terminator	

loaded from [Arrow.com](#)

Alignment Aids : **Alignment Gauge,
Camera**

Statement of
Compliance

[Statement of Compliance pdf](#)

Compatible Parts



TE Part # 1803095-3
**FLOATING SHEAR,
FRONT**

In-Stock

[View Product](#)



TE Part # 2119805-1
**SHEAR HOLDER,
FRONT, CUT**

In-Stock

[View Product](#)



TE Part # 2119806-1
INSERT, SHEAR

In-Stock

[View Product](#)



TE Part # 1-1633965-3
**CRIMPER, INSUL O
PREMIUM**

In-Stock

Need help?



Our team is on stand-by and ready
to help with your order.

[CHAT NOW](#)



ABOUT TE CONNECTIVITY

[Our Company](#)

[Events](#)

[TE News Center](#)

[Careers](#)

[Investors](#)

[Corporate
Responsibility](#)

[Terms and Conditions
of Sale](#)

FOR PARTNERS

[Distributors](#)

[Suppliers](#)

SUPPORT

[Customer Service](#)

[Find Authorized Distributors](#)

[Shop Online in the TE Store](#)

[Product FAQs](#)

CALL US

**SELE
LANG**

[United States](#)

[Germany \(DE\)](#)

[China \(中文\)](#)

[Japan \(日本語\)](#)

[Find Your Country/Region](#) ▼

[Terms of Use](#) | [Privacy](#) | [Cookie Policy](#) | [Accessibility](#) | [Site Map](#) |

© 2018 TE Connectivity. All Rights Reserved.

