


RoHS
Compliant

VERSION	DESCRIPTION	DATE
1.0	New Release	2017/3/30



PART NO	DRAWING NO	CABLE LENGTH "L"	COLOR
913M-2-3-00100-PL	671-454-A	1000±100	Aqua
913M-2-3-00200-PL	671-454-B	2000±100	Aqua
913M-2-3-00300-PL	671-454-C	3000±100	Aqua
913M-2-3-00500-PL	671-454-D	5000±100	Aqua
913M-2-3-00700-PL	671-454-E	7000±100	Aqua
913M-2-3-01000-PL	671-454-F	10000±100	Aqua
913M-2-3-01500-PL	671-454-G	15000±100	Aqua
913M-2-3-02000-PL	671-454-H	20000±100	Aqua
913M-2-3-02500-PL	671-454-I	25000±100	Aqua

NOTES:
Insertion loss < 0.3 dB

CnC Tech, LLC Industrial Cable and Connector Technology					
		TITLE	Patch Cord, LC-ST,MM-50/125 OM3, Duplex, OFNP, aqua, 2.0mm, xxM		
UNIT		P/N	above	DRAWN BY	
unless otherwise stated Tolerances mm angular XXX.XX ±0.3 ±2° XX.XX ±0.2 X.XX ±0.1		Customer P/N	913M-2-3-0xxxx-PL	CHECK BY	
SIZE		SCALE	PAGE	1/1	APPROVAL BY
A4		Free			

6	Dust Cover
5	Shrinkage Tube
4	$\frac{1}{2}$ Code
3	ST MM Connector (Metal housing Red/black boot)
2	LC MM Duplex Connector (Beige housing White boot)
1	2.0mm,Duplex,MM-50/125 OM3, OFNP, Optical Fiber Cable(Aqua)
No.	Description