








-Insertion loss must be tested 100%
-Return loss must be tested at least
by random samples



4	Hybrid cable 2xFO+3x2.5/3.5	33 57 211 020 5001	20 (± 0.20)m
3	Hybrid cable 2xFO+3x2.5/3.5	33 57 211 010 5001	10 (± 0.10)m
2	Hybrid cable 2xFO+3x2.5/3.5	33 57 211 005 5001	5 (± 0.05)m
1	Hybrid cable 2xFO+3x2.5/3.5	33 57 211 001 5001	1 (± 0.01)m

Cont No.	Type of cable	Part-No.	Dim. a
----------	---------------	----------	--------

		All Dimensions in mm Original Size DIN A 3			Techn. Character.		Nicht tolerierte Maße/	
		Mod.	Dat.	Name	Maßstab/Scale		Hybrid cable assembly, FO 2xG50/125 + POWER 3x2.5/3.5, 2xHAN3A, LC duplex MM, 3xpower AC	
		HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP					TB 33 57 211 xxx 5001	
							Sub.	Sub