

Technical data sheet

Article number:
111-01960

T18R



Product Group	Cable ties for outdoor use (UV-resistant)
Product Family	T-Series in PA66W/UV black
Material	Polyamide 6.6, UV-resistant (PA66W)
Colour	Black (BK)
Bundle Ø max.	22 mm
Bundle Ø min.	1.5 mm
Flammability	UL 94 V2
Halogen-free	Yes
Height (H)	3.7 mm
Length (L)	100.0 mm
Min.Tensile Strength	80 N
Operating Temperature	-40 °C to +85 °C, (+105 °C, 500 h)
Package Content packed in	pcs.
Pack Cont.	100 pcs.
Releasable Closure (Yes/No)	No
Specifications	ANSI/UL 62275, csa-C22.2 no. 62275
Thickness (T)	1.0 mm
Toothing (Serration)	Inside Serrated
UL-File Number	E85319
Variant	Inside Serrated
Weight/Unit	0.000327 kg
Width (W)	2.5 mm

