
DATE	REV	ECN	APP'D. BY
11/22/21	A0	11896	AB
09/13/22	A1	12042	GWL



Notes:

1) 8P8C MODULAR PLUG, GOLD PLATING 50μ" ON CONTACTS,

2) CABLE CONSTRUCTION:
   - 4 TWISTED PAIRS MINI CAT. 6 28AWG UTP, OD 3.6MM,
   - PVC JACKET

3) TRANSPARENT BOOT (OD 4.5MM)

4) SNAGLESS STRAIN RELIEF

5) EACH CABLE ASSEMBLY TO BE INDIVIDUALLY BAGGED.

6) 100% TRANSMISSION TESTED FOR PERFORMANCE.

7) MARKING:
   (UL) E305668 TYPE CM 28AWG 75°C C(UL) E305668 CM 28AWG 75°C ETL VERIFIED ANSI/TIA-568.2-D MINI UTP CAT. 6 RoHS COMPLIANCE MSL BATCH NO.

8) BLUE IS THE STANDARD CABLE COLOR. OTHER LISTED COLORS MAY HAVE A MINIMUM ORDER QUANTITY.

P/N Key:


BC-R6Uyxxx**F**

UOM
F = Feet

Length		Tolerance
XXX	Feet	Inch
000 ~ 003	0 ~ 3	± .8
004 ~ 006	4 ~ 6	± 1.2
007 ~ 050	7 ~ 50	± 1.6

Color
E = Blue (Standard)
K = Black
N = Green
G = Gray
R = Red
Y = Yellow
W = White
P = Purple
O = Orange

Wiring Map: 568B Standard



Example Part Numbers

Feet		
P/N	Color	Length
BC-R6UE001F	Blue	1'
BC-R6UE010F	Blue	10'
BC-R6UE015F	Blue	15'

For Part Numbers Not Shown Follow Part Number Key Format

RoHS 2002/95/EC

THIRD ANGLE PROJECTION

DO NOT SCALE DRAWING

DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE

DIMENSIONS: INCHES [METRIC]

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ±.005 [0.13] ANGLES ARE ± 1°

SHEET NO. 1 OF 1

206 Van Vorst Street
Jersey City, NJ 07302
+1 201 432 0463
http://www.belfuse.com

TITLE: BEL PATCHCORD ASSEMBLY, C6 U/UTP, 28 AWG

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF BEL FUSE, INC. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF BEL FUSE, INC.

DRN BY:	GWL	DATE	11/17/21
APPD BY:	AB	DATE	11/22/21
DWG NO.	CT999272	REV.	A1

ASSEMBLY FORMAT REV. 6/3/05

AutoCAD

Downloaded from Arrow.com.
Please read our datasheet & drawing disclaimer here.