

## Data Sheet | Item Number: 890-601

Fixing pin; 5 mm Ø, for 1.5 ... 2.5 mm mounting plates; Plastic; black

<https://www.wago.com/890-601>



Color: ■ black

### Mounting accessories WINSTA® MINI

When using the mounting accessories from the WINSTA® MINI product line, straightforward electrical installation is guaranteed. With WAGO, you can enjoy the advantages of a large selection of expansions for the WINSTA® product line. Due to its particularly compact dimensions, our WINSTA® MINI Pluggable Connection System with Push-in CAGE CLAMP® spring pressure connection technology is specifically suitable in very tight spaces, i.e., for installations when very little room is available.

Push-in CAGE CLAMP® spring pressure connection technology – pluggable installation instead of laborious screw connections!

The WINSTA® Pluggable Connection System is perfectly tailored to the strict requirements of building installation. It makes electrical installation pluggable, and thus faster, even more reliable, and error-free. Using this pre-assembled system decreases time spent on assembly and installation errors at the construction site. Now you can also reduce installation costs without compromising safety and quality: with protection against mismatching eliminates the need for servicing and prevents unnecessary downtime.

- compact design for conductors with a cross-section up to 1.5 mm<sup>2</sup>
- quick replacement of defective units during ongoing operation

### Notes

General safety information

#### **NOTICE: Observe installation and safety instructions!**

- Nur von Elektrofachkraft oder einer für die Tätigkeit elektrisch unterwiesenen Person (EUP nach DIN VDE 0105-100) anzuwenden!
- Nicht unter Spannung/Last installieren!
- Nur für bestimmungsgemäßen Gebrauch einsetzen!
- Nationale Vorschriften/Normen/Richtlinien beachten!
- Technische Daten der Produkte beachten!
- Auf die richtige Polbelegung achten!
- Keine beschädigten/verschmutzten Komponenten verwenden!
- Leiterarten, -querschnitte, Abisolierlängen und Leitungsdurchmesser beachten!
- Leiter bis zum Anschlag einführen!
- Nur mit Verriegelungsklinke und Zugentlastung verwenden!
- Originalzubehör verwenden!

**To be sold only with installation instructions!**

### Physical data

Width	9 mm / 0.354 inches
Depth	9 mm / 0.354 inches

### Material data

Note (material data)	<a href="#">Information on material specifications can be found here</a>
Color	black
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0 MJ
Weight	1 g

### Environmental requirements

Processing temperature	-5 ... +40 °C
Continuous operating temperature	-35 ... +85 °C
Note on continuous operating temperature	Insulating parts for temperatures ≤ 105 °C

### Commercial data

Product Group	20 (Winsta)
PU (SPU)	250 pcs
Packaging type	Box
Country of origin	CN
GTIN	4045454636982
Customs tariff number	39269097900

### Product Classification

UNSPSC	31162809
eCl@ss 10.0	27-44-06-92
eCl@ss 9.0	27-44-06-92
ETIM 9.0	EC002863
ETIM 10.0	EC002863
ECCN	NO US CLASSIFICATION

### Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

### Approvals / Certificates

#### Approvals for marine applications



Approval	Standard	Certificate Name
LR Lloyds Register	EN 61535	LR23317167TA

### Downloads

#### Environmental Product Compliance

##### Compliance Search

Environmental Product  
Compliance 890-601



### Documentation

#### Bid Text

890-601	13.01.2015	doc 22.00 KB	
890-601	19.02.2019	xml 2.62 KB	

### CAD/CAE-Data

#### CAD data

2D/3D Models 890-601



#### CAE data

WSCAD Universe  
890-601

