



Part Number : [1062250004](#)
Product Description : MPO Female-to-MPO Female Fiber Optic Trunk Cable Assembly, 50/125µm, 4.80mm, Multimode, 12 Fiber, Plenum, OM3, 100.0m Length, Aqua Cable
Series Number : 106225
Status : Active
Product Category : Fiber Optic Cable Assemblies




Documents & Resources

Drawings
[1062250004_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Fiber Optic Cable Assemblies
Series	106225
Description	MPO Female-to-MPO Female Fiber Optic Trunk Cable Assembly, 50/125µm, 4.80mm, Multimode, 12 Fiber, Plenum, OM3, 100.0m Length, Aqua Cable
Connector to Connector	MPO-to-MPO
Mode	Multimode
Product Name	MPO
UPC	191128249867

Physical

Boot Type	Straight
Cable Length	100.0m
Cable Size	4.80mm
Fiber (Core/Cladding)	50/125µm
Net Weight	2254.976/g
Single Ended	No
Wire/Cable Type	12 Fiber OM3 Plenum

This document was generated on Apr 03, 2025
