






REV.	DATE	DESCRIPTION
NC	11/08/99	INITIAL RELEASE
A	10/01/06	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:
0.5 - 8mm ± 0.20mm
8 - 30mm ± 0.40mm
30 - 120mm ± 0.50mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:
.020 - .315 = ± 0.007"
.315 - 1.180 = ± 0.015"
1.180 - 4.724 = ± 0.020"

DO NOT SCALE DRAWING

APPROVALS	DATE
DRAWN G.R.S.	10/01/06
CHECKED	
ISSUED	
SHEET 1 OF 1	
CAD FILE	C:/112/112644.DWG

Amphenol Connex

PART DESCRIPTION
**BNC CRIMP PLUG
(FOR RG-179/U DOUBLE BRAID CABLE)**

PART NO. **112644**

DWG. NO.	REV.	SIZE	SCALE
112644.DWG	A	A	NA

DESCRIPTION	MATERIAL	FINISH	QTY
8			
7			
6			
5			
4 FERRULE	COPPER	NICKEL	1
3 CONTACT PIN	BER. COPPER	GOLD	1
2 INSULATOR	DELIN	NATURAL	1
1 BODY	BRASS	NICKEL	1