
AMPHENOL PN
10197766-1030LF



WIRING LIST		
CON1		**CON2**
PIN1	RED	PIN1
PIN2	GRAY	PIN2
PIN3	GRAY	PIN3
PIN4	GRAY	PIN4
	• • •	
PIN9	GRAY	PIN9
PIN10	GRAY	PIN10

NOTES:

1. ALL CABLE ASSEMBLIES SHALL BE TESTED 100% FOR CONTINUITY AS DEFINED IN WIRING LIST.
2. UNLESS OTHERWISE SPECIFIED ALL CABLE ASSEMBLIES SHALL BE TESTED:

   HI-POT: DC 300V/10ms.

   DIELECTRIC RESISTANCE: 10M Ohms MIN.

   CONNECTION RESISTANCE: 3 Ohms MAX.
3. LEAD FREE PRODUCTS MEET EUROPEAN UNION DIRECTIVES.

Qty	Unit	Description	Item
/	M	Flat Cable, UL2678, 30AWG*10C, PITCH: 0.635MM	2
2	EA	IDC CONN.: 1.27PITCH, 2X5PIN, 0.25um GOLD AT CONTACT, BLACK, 20021444-00010T4LF	1

ltr	ecn no	dr	date
A		Jacob	3/23'26

mat'l. code

surface ISO 1302 √ | tolerance ISO 406 ISO 1101

tolerances unless otherwise specified: angles | linear

projection | MM | scale N/A

dr	Jacob Ding	3/23'26
engr	Jacob Ding	3/23'26
chr	TIM YAO	3/23'26
appd	TIM YAO	3/23'26

Amphenol FCi

Cable Assembly

title: IDC CABLE ASSEMBLY

dwg no: 10197766-1030LF | sheet 1 of 1 | size A3

type: Customer Drawing

sheet index | revision A | sheet

form: A3-2016-02-24

© 2016 AFCI

Amphenol FCi

Downloaded from Arrow.com.

PDS: Rev :A STATUS:Released Printed: Mar 25, 2026