

## Pre-Configured Unshielded Cat6 4-Port Surface-Mount Box, 110 IDC, RJ45, White, TAA

MODEL NUMBER: **N236-004-WH**



Pre-configured self-contained Cat6 surface-mount box provides up to four RJ45 connections in applications where in-wall installation is impossible. Recommended for audio/video, voice and Ethernet applications.

### Description

The N236-004-WH Pre-Configured Unshielded Cat6 4-Port Surface-Mount Box features four RJ45 female connectors as a fast, easy and cost-effective tool for expanding your Cat5e/6 audio/video, voice or Ethernet network. The ABS UL 94V-0 flame-retardant housing mounts practically anywhere, including a wall or baseboard, using the included mounting screws or double-sided adhesive tape.

Just snap open the top cover to terminate up to four 22–26 AWG Cat5e/6 copper cables using a standard 110 IDC punchdown tool (such as N046-000). The termination blocks are color-coded for easy T568A or T568B wiring. Zip ties are included for neatly securing the cables to the Cat6 surface-mount box, which features rear routing slots to allow the box to be installed flush against a wall or ceiling.

Snap the cover back on, and connect up to four Cat5e/6 cables to the pre-installed RJ45 keystone jacks with 50-micron gold-plated contacts for maximum conductivity and minimum data loss. The N236-004-WH offers great flexibility in placement, especially in applications where in-wall box and wire installation is impossible.

### Features

#### 4-Port Surface-Mount Box Completes A/V, Voice and Ethernet Applications

- Connect up to 4 Cat5e/6 cables to pre-installed RJ45 keystone jacks
- 50 m gold-plated contacts for maximum conductivity
- Durable ABS UL 94V-0 flame-retardant housing designed to last
- Complies with ANSI/TIA/EIA 568B standards

#### Ideal for Applications in Which In-Wall Installation Is Impossible

- Recommended for use with 22–26 AWG Cat5e/6 cabling
- Uses standard 110 IDC punchdown termination
- Termination blocks color-coded for T568A/B wiring compatibility
- Zip ties included for neatly securing cables through rear routing slots

#### Easy to Mount Almost Anywhere

- Mounting screws and double-sided tape are included

### Highlights

- Uses standard 110 IDC punchdown termination
- Recommended for use with 22–26 AWG Cat5e/6 cabling
- Termination blocks color-coded for T568A/B wiring compatibility
- Durable ABS UL 94V-0 flame-retardant housing designed to last
- 4 RJ45 jacks with gold-plated contacts for maximum conductivity

### Package Includes

- N236-004-WH Pre-Configured Unshielded Cat6 4-Port Surface-Mount Box
- (2) Double-sided tape
- (4) Cable ties
- (2) Mounting screws
- Quick Start Guide

## Specifications

OVERVIEW	
UPC Code	037332206978
Technology	Cat5/5e; Cat6
Country/Region	Global
CONNECTIONS	
Number of Ports	4
PHYSICAL	
Color	White
Total Number of Ports	4
FEATURES & SPECIFICATIONS	
Antibacterial	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.