
Your Expert Partner for **Human Machine Interfaces**

Actuator


704.730.1



https://www.eao.com/component/704.730.1/en/ac...

Downloaded from Arrow.com.

Your product:



704.730.1
Actuator

FRONT

Front dimension:	30 mm x 30 mm
Front form:	Square

MOUNTING

Design:	Raised
Mounting type:	Panel mounting

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the “Standards for low-voltage switching devices” DIN EN 60947-1

MECHANICAL CHARACTERISTICS

Weight:	0.005 kg

AMBIENT CONDITION

IP Protection:	IP65 front side
Operating temperature:	– 40 °C ... + 55 °C
Storage temperature:	– 40 °C ... + 85 °C

CERTIFICATE


REACH:	REACH compliant
RoHS:	RoHS compliant

Downloaded from Arrow.com.

OTHER


Short Description:	Actuator, 30 mm x 30 mm, Square
Housing colour:	Grey
Housing material:	Plastic

Wiring diagrams:




Mounting cut-outs:

Downloaded from Arrow.com.




A = Screw terminal
B = Push-in terminal (PIT)




A = Screw terminal
B = Push-in terminal (PIT)
C = Plug-in terminal 6.3 mm x 0.8 mm
D = Double plug-in terminal 6.3 mm x 0.8 mm

Dimension drawings:

Downloaded from Arrow.com.



A = Screw terminal



X = Screw terminal

Downloaded from Arrow.com.