Part Number : 5033082412
Product Description : SlimStack Board-to-Board Plug, 0.40mm Pitch, 0.70mm Mated Height, 2.60mm Mated Width, 24 Circuits
Series Number : 503308
Status : Obsolete
Product Category : Board-to-Board Connectors



Documents and Resources

Drawings

5033082412_sd.pdf

Specifications

5033040001-000.pdf

5033040003-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Obsolete

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Board-to-Board Connectors
Series	503308
Description	SlimStack Board-to-Board Plug, 0.40mm Pitch, 0.70mm Mated Height, 2.60mm Mated Width, 24 Circuits
Application	Board-to-Board
Component Type	Plug
Product Name	SlimStack
UPC	191128129534

Electrical

Current - Maximum per Contact	0.3A
Voltage - Maximum	50V AC (RMS)/DC

Physical

Breakaway	No
Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Black
Durability (mating cycles max)	30
Glow-Wire Capable	No
Lock to Mating Part	No
Mated Height	0.70mm
Mated Width	2.60mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold

Obsolete

Downloaded from Arrow.com.

Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	9.732/mg
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	No
Pitch - Mating Interface	0.40mm
Pitch - Termination Interface	0.40mm
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
0.40mm Pitch SlimStack Board-to-Board Vertical Receptacles	503304

This document was generated on Sep 23, 2026

Obsolete

Downloaded from Arrow.com.