**Part Number :** 5052782833
**Product Description :** 0.50mm Pitch Easy-On FFC/ FPC Connector, 1.90mm Height, Single Bottom Contact (FS19), Right-Angle, Surface Mount, ZIF, 28 Circuits
**Series Number :** 505278
**Status :** Obsolete
**Product Category :** FFC / FPC Connectors



Obsolete

## Documents and Resources

### Drawings

5052782833_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

### Specifications

5052780000-000.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Obsolete |
| Category | FFC / FPC Connectors |
| Series | 505278 |
| Description | 0.50mm Pitch Easy-On FFC/FPC Connector, 1.90mm Height, Single Bottom Contact (FS19), Right-Angle, Surface Mount, ZIF, 28 Circuits |
| Comments | Black Actuator |
| Product Name | Easy-On |
| UPC | 889056034296 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 0.5A |
| Voltage - Maximum | 50V |

### Physical

| | |
|---|---|
| Actuator Type | Front Flip |
| Circuits (Loaded) | 28 |
| Color - Resin | Beige |
| Contact Position | Bottom |
| Durability (mating cycles max) | 20 |
| Mated Height | 1.90mm |
| Material - Metal | Phosphor Bronze |

Obsolete

Downloaded from Arrow.com.

| | |
|---|---|
| Material - Plating Mating | Tin-Silver-Bismuth |
| Material - Plating Termination | Tin-Silver-Bismuth |
| Material - Resin | Liquid Crystal Polymer (LCP) |
| Net Weight | 224.380/mg |
| Orientation | Right Angle |
| Packaging Type | Embossed Tape on Reel |
| PCB Locator | No |
| PCB Mounting | Surface Mount |
| PCB Retention | Yes |
| Pitch - Mating Interface | 0.50mm |
| Pitch - Termination Interface | 0.50mm |
| Plating min - Mating | 1.016µm |
| Plating min - Termination | 1.016µm |
| Polarized to PCB | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +85°C |
| Wire/Cable Type | FFC/FPC |

Obsolete

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| 0.50mm Pitch Premo-Flex FFC Jumpers with Latching Ears | 15466 |
| 0.50mm Pitch Premo-Flex FFC Jumpers | 15166 |
| 0.50mm Pitch Premo-Flex FFC Jumpers | 15266 |
| 0.50mm Pitch Premo-Flex FFC Jumpers | 98266 |
| 0.50mm Pitch Premo-Flex FFC Jumpers | 15366 |



Downloaded from Arrow.com.