

Product Line

- DeepTronica

>
- Single Pair Ethernet

>
- ZConnect

>
- Ceres

>
- X-Lok

>
- M Series

>
- FLOS & FLOS+

>
- Power

>
- RBL

>
- HS-Lok

>
- NMEA 2000

>
- Mini

>
- Micro

>
- Accessory

>
- Heavy Duty Shielded

>
- RJ

>
- USB

>
- SSL

>
- HDMI

>
- DVI

>
- Fiber Optic

>
- RF

>
- Cable Joiner

>
- Cable Gland

>
- Pressure Relief Vent

>
- LED Light Guide

>
- D-Sub

>



HMCP-05BFFT-SL8001

Operating Temperature: -20°C ~ +85°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: N/A

Certificate: NMEA 2000

You must login first for view the price

Quantity

- 1 +

Check Stock

Add to Cart

Inquiry

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

NMEA 2000,...

HMCP-05BMMT-...

-20°C ~ +85°C

- 0 +

NMEA 2000, Micro..

HPC-000505-0M...

-20°C ~ +80°C

- 0 +

NMEA 2000, Micro..

HPC-000505-0M...

-20°C ~ +80°C

- 0 +

NMEA 2000, Micro..

HPC-000505-0M...

-20°C ~ +80°C

- 0 +

NMEA 2000, Micro..

HPC-000505-0M...

-20°C ~ +80°C

- 0 +

NMEA 2000, Micro..

HPC-000505-0M...

-20°C ~ +80°C

- 0 +

Add to Cart

Inquiry

Specifications	Download / CAD
Nominal Current	Connector Type
4A	Terminator
Shielded	No. of Contacts
Plastic, Non-shielded	05
Connector Gender	Backshell
Female	Straight
Mating Style	IP Rating
Screw Thread	IP68
Assembly Style	
N/A	
More Options	

People Also Bought

- HMCP-05BFFT-...
- BD-02BFMM-SR6A05
- MSAP-08BMMM-...
- CAP-WTAFSMA1
- AB-BB02HL-BB8R-...