HellermannTyton

Specification Sheet

Part Number: 151-10916



2- or 4-way entry options for the Q Tie, offering flexibility and stability

Q Tie Mount with Adhesive, 1.6 x 1.6 x 0.26", 4 way entry for Q18 thru Q120 ties, PA66, Black, 50/pkg

Article Number	151-10916
Type	QM40A
Color	Black (BK)
Quantity Per	pack
Product Description	Q Mounts are designed to work exclusively with the Q Tie cable tie series. This mounting component is available with adhesive or can be secured with screws. The Q Mount allows either a 2- or 4-way entry for the Q Tie, providing a quick and simple insertion into the mount. Once in place, the Q Tie will not slip out, even in vertical mounting applications.
Short Description	Q Tie Mount with Adhesive, 1.6 x 1.6 x 0.26", 4 way entry for Q18 thru Q120 ties, PA66, Black, 50/pkg

Downloaded from Arrow.com.

Global Part Name	QM40A-PA66-BK
Length L (Imperial)	1.6
Length L (Metric)	40.0
Fixation Method	Adhesive
Width W (Imperial)	1.6
Width W (Metric)	40.0
Height H (Imperial)	0.26
Height H (Metric)	5.5
Cable Tie Width Max (Imperial)	0.31
Cable Tie Width Max (Metric)	8.4
Mounting Hole Diameter D (Imperial)	0.16 "
Mounting Hole Diameter D (Metric)	4.1 mm
Mounting Hole Centers (Imperial)	1.19
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66

Downloaded from Arrow.com.

Adhesive	Synthetic rubber with base of polyethylene foam
Flammability	UL 94 V-2 (excluding adhesive)
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Adhesive Operating Temperature	-40°F to +140°F (-40°C to +60°C)
Operating Temperature	-40°F to +140°F (-40°C to +60°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.