







Performance class:	4	-->200 mating/un-mating
6	--> 500 mating/un-mating	



PC card drilling dimensions(after plating)
(thickness 2.40±0.20mm)



FEMALE DELTA-D
STRAIGHT , SOLDER TYPE

mat'l. code				surface			tolerance			projection		product family	
-				ISO 1302			✓					D-SUB	
				tolerances unless otherwise specified			ISO 406 ISO 1101						
ltr	ecrn	no	dr	date								title	
G	EX1-21654	AB	2015-10-26	angles				.0±0.1		MM		FEMALE DELTA-D	
H	EX1-42817	ACJ	2021-10-18	linear				.00±0.05		↔		STRAIGHT , SOLDER TYPE	
				0±1°				.000±0.005		scale 2:1			
				dr		LELEON		1992-09-16				dwg no	
				engn		GREGAR MATHEW		2021-10-18		Amphenol FCI		sheet 1 of 1	
				chr		GREGAR MATHEW		2021-10-18				C01 - 8646 - 0125	
				apdd		SAMOU KURIAKOSE		2021-10-18				A3	
sheet	revision			H									size
index	sheet			1									