**Part Number :** 732870650
**Product Description :** N Type Termination, Plug, Straight, 18 GHz, 2 Watt, without Chain
**Series Number :** 73287
**Status :** Active
**Product Category :** RF / Coaxial Connectors



## Documents and Resources

### Drawings

732870650_sd.pdf

STEP AP242

SOLIDWORKS

Creo

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | RF / Coaxial Connectors |
| Series | 73287 |
| Description | N Type Termination, Plug, Straight, 18 GHz, 2 Watt, without Chain |
| Application | RF |
| Keyword | Termination, Terminations |
| Product Name | N,Termination |
| Style | Coaxial Termination |
| Type | Medium |
| UPC | 198282629238 |

### Electrical

| | |
|---|---|
| Average Power Max (Watts) | 2 |
| Frequency | 18 GHz |
| Impedance | 50Ω |
| VSWR (max) | 1.25:1 |

### Physical

| | |
|---|---|
| Body Style | Without Chain |
| Cable Attachment | N/A |
| Gender | Plug |
| Keying to Mating Part | N/A |
| Orientation | Straight |
| Packaging Type | Bag |
| Panel Mount | No |

Downloaded from Arrow.com.

| | |
|---|---|
| Panel Mount Method | N/A |
| PCB Mounting | N/A |
| Reverse Polar | No |
| Wire/Cable Type | N/A |



Downloaded from Arrow.com.