

®
Thermofit Molded Parts
Specification Control Drawing
Limited Distribution

Part Number : 221A011
Description : Boot, 90°

NOTES

1. All dimensions are in inches
[millimeters]
2. Dimensions appearing in table
are as follows:
a - As Supplied
b - After Unrestricted Recovery
3. Coating is optional. As supplied
dimensions appearing in table are
for uncoated parts. When coating
is added, entry diameters will be
reduced by .06 max.




TABLE OF DIMENSIONS

PART NUMBER	H		J		P ±10% b	S ±10% b	J0 ±10% b	W ±.03 b
	Min a	Max b	Min a	Max b				
221A011	.86 [21.8]	.31 [7.8]	.86 [21.8]	.22 [5.6]	1.50 [38.1]	.81 [20.6]	.60 [15.2]	.05 [1.3]

Raychem

RAYCHEM CORPORATION
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

Revision : B
Date : 1/27/99

Part Number : 221A011
Description : Boot, 90°

®
Thermofit Molded Parts
Specification Control Drawing
Limited Distribution

Part Number : 221A011
Description : Boot, 90°

COMPATABILITY CHART					
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.	COATING DESCRIPTION
-50	Flexible VPB	RT-1313			
-51	Flexible EPB	RT-1321	/164	S-1124	Adhesive

ORDERING INFORMATION

221A011 -XX -XX /XXX

Base part number

Material dash number
(See Compatability Chart)

Modification number
(If necessary, see front of scd binder
for a complete list)

Adhesive slash number
(If necessary, see Compatability Chart)

THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE; CONSULT YOUR
NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION

If this document is printed it becomes uncontrolled.
Check for the latest revision.

Raychem

RAYCHEM CORPORATION
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

Revision : B
Date : 1/27/99

Part Number : 221A011
Description : Boot, 90°

CAD FILE MP99030