



**Part Number :** [2070190004](#)

**Product Description :** Mini-Fit Sigma Sealed Cap for 4 Circuit Plug Housing

**Series Number :** 207019

**Status :** Active

**Product Category :** Connector Accessories



---

## Documents and Resources

### Drawings

[2070190004\\_sd.pdf](#)

[2070180000-PK-000.pdf](#)

[2070190004\\_stp.zip](#)

### Specifications

[2070170000-AS-000.pdf](#)

[2070170000-PS-000.pdf](#)


[2070170000-TS-000.pdf](#)

[2070170001-TS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Connector Accessories
Series	207019
Description	Mini-Fit Sigma Sealed Cap for 4 Circuit Plug Housing
Component Type	Cap
Product Name	Mini-Fit Sigma Sealed
UPC	193264428557

### Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Lock to Mating Part	Yes
Material - Resin	Thermoplastic Elastomer
Net Weight	6.140/g
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C

## Mates With / Use With

### Use with Part(s)

Description	Part Number
-------------	-------------

Mini-Fit Sigma Sealed Plug  
Housing, Dual Row, 4.20mm  
Pitch, 4 Circuits, UL94V-0, Natural

2070170004

---

This document was generated on Jun 10, 2026