


THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

NOTES:

- SPECIFICATION:  
JACKET: SILICONE. MULTI-LAYER, 1ST LAYER WHITE; 2ND LAYER "COLOR" OD: .154±.008 (3.9 mm)  
CONDUCTOR: BARE COPPER, STRANDING 651 x 0.07 mm = 2.50 mm<sup>2</sup>, 13 AWG.
- RATING:  
VOLTAGE: 1,000 V CAT IV PER IEC 61010-031  
CURRENT: 36 A MAX.  
TEMPERATURE: -60° C TO +180° C.
- AVAILABLE IN 3 STANDARD LENGTHS AND 6 COLORS - SEE MODEL NUMBER BELOW.

REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
—	CLASS A RELEASED	7/11/99	
A	UPDATED FORMAT w/ CAGE CODE	4/18/04	



**MODEL NUMBER**

**CT2844-#-XXX**

COLOR: 0 - BLACK  
2 - RED  
4 - YELLOW  
5 - GREEN  
6 - BLUE  
9 - WHITE

LENGTH: 10 - 10 m PACKAGE  
50 - 50 m SPOOL  
100 - 100 m SPOOL

THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ± 1/32 .XX ± .02 .XXX ± .005 DO NOT SCALE DRAWING		CONTRACT NO.		<b>Cal Test Electronics</b> 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610			
		MATERIAL		APPROVALS		DATE		TITLE <b>WIRE, TEST LEAD, SILICONE JACKET, 2.50 mm<sup>2</sup>, 13 AWG, 36 A</b>	
				DRAWN WDH		7/11/99			
				CHECKED					
				ENGR.					
NEXT ASSY		USED ON		DESIGN ACTIVITY					
APPLICATION									
						SIZE <b>A</b>		CAGE CODE <b>43F45</b>	
						DWG. NO. <b>P284400</b>		REV. <b>A</b>	
						SCALE NONE		SHEET 1 OF 1	