Part Number : 1060051100
Product Description : QSFP + MTP Loopback, Multimode, 12 Fiber, 50/125µm, QSFP+ Pin Out
Series Number : 86290
Status : Active
Product Category : Fiber Optic Cable Assemblies



Documents and Resources

Drawings

1060051100_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane; 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Fiber Optic Cable Assemblies
Series	86290
Description	QSFP + MTP Loopback, Multimode, 12 Fiber, 50/125µm, QSFP+ Pin Out
Connector to Connector	N/A
Mode	Multimode
Product Name	QSFP Plus,QSFP+
UPC	883906279806

Physical

Boot Type	N/A
Cable Length	LOOPBACK
Cable Size	50/125µm
Fiber (Core/Cladding)	50/125µm
Net Weight	95.600/g
Single Ended	Yes
Wire/Cable Type	Ribbon Cable

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Downloaded from Arrow.com.

Description	Part Number
EMI MPO Adapters	106114
MTP Adapter Assemblies	106181

Downloaded from Arrow.com.