Johanson Part Number Information

08-02-2023

Johanson Part Number:	LRC0603CS5N6GV001T	Johanson Company:	**Johanson Technology Inc.**
Legacy P/N:	L-14C5N6SV4T	NCNR:	No
Description: Ceramic Inductor, 0603, 5.6nH±0.3nH, 300mA, Ni/Sn (RoHS), No Mark, 7" Reel Paper Tape		Thickness (Max):	0.039
Life Cycle Stage:	Active - Production	Thickness (Min):	0.023
AEC Q200 Qualified:	No	End Band (Max):	0.016
Schedule B:	8504.50.0000	Standard Item:	No
Harmonization Code:	8504.50.40.00	Lead Time Typical (Weeks)*: *This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.	14
ITAR:	No	Length (Min):	0.057
ECCN:	EAR99	Length (Max):	0.069
RoHS Compliance:	Yes, RoHS 10/10	Width (Min):	0.023
REACH:	Yes	Width (Max):	0.039
Country of Origin:	TW	Part Weight (mg):	3.980
Product Family:	Inductors	Packaged Weight (lb) Arm:	0.300
Product Subfamily:	Ceramic Inductors	Packaging:	7" Reel Paper Tape
Tolerance:	±0.3nH	Packaging Qty:	4000
Termination:	Ni/Sn (RoHS)	Operating Temp Range:	-40°C to + 100°C
Marking:	No Mark	Storage Temp Range (Packaged):	-10°C to +40°C
Product Release Date:	04 January, 2006	Storage Temp Range (Non Operating):	-40°C to +125°C

Web Page Link:
https://www.johansontechnology.com/ceramic-inductors

Download this information page

© All rights reserved. Johanson Technology

Downloaded from Arrow.com.