

Switchcraft®

# 06AL5FX

DIN Cable Mount Connector, female receptacle with ground contact, 5 contacts at 180

In stock

Drawings: PDF STEP

Symbol, Footprint, 3D Model

Buy Now

< View More From This Family

Specifications | Videos | Documents

## Configuration

- Number of Conductors: 5
- Mounting Type: Cord
- Gender: Female
- Contact Size: 22 AWG
- Termination Style: Solder Cup
- Contact Plating: Tin
- Color: Nickel
- Handle Material: Soft Plastic
- Packaging Type: Bulk
- Standard Connector Type: DIN
- Special Feature: Ground Key-Rib

## Electrical

- Contact Resistance: 0.01 Ohms
- Dielectric Withstanding Voltage: 500 Volts
- Current Rating: 3 Amps

## Mechanical

- Operating Force: 9 lbs

## Compliance

- RoHS Compliant: Compliant
- REACH Compliant: Compliant
- Brand: Switchcraft

## Dimensional

- Cable Opening: 0.39 in



© 2023 Switchcraft and Conxall. All Rights Reserved.

Downloaded from Arrow.com.