MUELLER® DATASHEET

BU-P2854-@

(Panel Mount 4mm Banana Jack, 10 Pack)



- BU-P2854 is a 10-pack of panel mountable 4mm banana jacks. Can be mounted to panels from 0.063” to 0.375” thick. Wire can be soldered to pin ends.
- Overall length 1.22” (31mm), OD = 0.5” (12.7mm)
  - Pole Threads: ¼-32 UNEF-2A
- Mounting: Mount thru panels up to 0.375” (9.52mm) thick with a Ø0.375” (9.52mm) hole.
- Material:
  - Contacts: Gold-plated brass
  - Insulators: Nylon
- Rating:
  - Current: 15 Amps
  - Voltage: Handheld 30 Vrms/60 Vdc
    Hands-free testing up to 2000 VDC max
  - Temperature: -50°C to 120°C
- Color: The “@” in the model number indicates color.
  Available colors are: -0 Black, -2 Red
- **10 banana jacks packaged per bag.**
- RoHS 3 compliant, exemption 6c

Mueller Electric Company
2850 Gilchrist Rd. Bld 5A
Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629
Phone: 330.780.2525
Fax: 330.780.2524

Downloaded from Arrow.com.