








PC board drilling dimensions
(after plating – thickness: 1.60 to 3.20 mm)



GENERAL CHARACTERISTICS AND ROHS INFORMATION:	
SEE DRAWING C01-8646-0001	

ROHS PART NUMBER	
200 matings	D50P90C4GV00LF
500 matinas	D50P90C6GV00LF

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family D-SUB			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
A	—	MPE	1994-06-24	angles	linear	.0±0.1			MALE CONNECTOR DELTA D 50 STRAIGHT PRESS FIT LOW PROFILE				
B	—	MPE	1995-05-09			.00±0.1							
C	—	MPE	1995-02-10			.000±0.1							
D	—	MPE	1996-07-25	dr	M PESSON	2007-09-06		Amphenol FCi	dwg no		sheet 1 of 1	size	
E	LS07-0232	MPE	2007-09-06	engr	MITHUN PAUL	2016-06-06			C01-8646-0257		A3		
F	ELX-I-24020	AAB	2016-06-06	chr	ATHUL A.B	2016-06-06							
				appd	BIJU K PAUL	2016-06-06				type Product Customer Drawing			
sheet index		revision sheet		F	1								