Specifications



Photo is representative





Eaton FP1005R1-R10-R

Eaton FP1005R inductor, 0.1 uH, 53 A Irms, 73 A ISAT, 0.42 mΩ resistance, SMT mounting, Ferrite, 2-pins, 950 qty.

General specifications	
PRODUCT NAME	Eaton FP1005R inductor
CATALOG NUMBER	FP1005R1-R10-R
UPC	051712543569
PRODUCT LENGTH/DEPTH	10.2 mm
PRODUCT HEIGHT	4.95 mm
PRODUCT WIDTH	7 mm
PRODUCT WEIGHT	1.45 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	53 A
ISAT	73 A
PACKAGE QUANTITY	950
MATERIAL	Ferrite
FREQUENCY RATING	Up to 2 MHz
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	0.42 mΩ
SERIES	FP1005R

Resources

SPECIFICATIONS AND DATASHEETS	Eaton FP1005R high current power inductors data sheet Eaton Specification Sheet - FP1005R1-R10-R

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.