



Part Number : 1301070034

Series Number : 130107

Product Category : Portable Lighting Accessories

Product Description : Super-Safeway Assembled Rubber Stringlight Lampholder with MAX-LOC Grips and Guard

Status : New Business Not Supported

Engineering Number : 310W

Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	New Business Not Supported
Category	Portable Lighting Accessories
Series	130107

Description	Super-Safeway Assembled Rubber Stringlight Lampholder with MAX-LOC Grips and Guard
NEMA Configuration	N/A
NEMA Rating	Rain Tight
Product Family	Lighting Accessories
Product Name	Super-Safeway
Type	Accessory
UPC	78678861218

## Electrical

Lamp Wattage - Maximum	200W
Lumens	2000
On/Off Switch	N/A
Voltage (Fixture) - Maximum	120VAC 60 HZ

## Physical

Bulb Type	Incandescent
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	46.48mm (1.830")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	99.06mm (3.900")
Lamp Type	A21
Length	180.34mm (7.100")
Material - Guard	N/A
Mounting Style	Stringer
Outlet	None
Packaging Type	Carton