

CD 40X80 - Cable duct

3240198

<https://www.phoenixcontact.com/us/products/3240198>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable duct for installation and mounting in control cabinets, gray, comprising upper part and mounting base, width: 40 mm, height: 80 mm, length: 2000 mm

Your advantages

- Predetermined breaking point enables tool-free, burr-free removal of bars
- Thanks to its leverage and special cutting geometry, the PPS CD cable duct cutter enables easy, burr-free cutting with minimum effort
- Easy, burr-free cutting with minimum effort using the CUTFOX-CD cable duct cutter
- The wide, diagonal heads of the cable duct bars make it easy to fit the cover and hold it securely in place
- Installed conductors are securely held in place by means of wire retaining clips that can be snapped onto bars on the side
- Plastic body-bound rivets enable easy fixing of cable ducts using the rivet setting tool

Commercial data

Item number	3240198
Packing unit	16 pc
Minimum order quantity	16 pc
Sales key	BE74
Product key	BE7431
GTIN	4046356459167
Weight per piece (including packing)	1,140 g
Weight per piece (excluding packing)	1,140 g
Customs tariff number	39259020
Country of origin	DE

CD 40X80 - Cable duct

3240198

<https://www.phoenixcontact.com/us/products/3240198>



Technical data

Product properties

Product type	Wiring duct
--------------	-------------

Dimensions

Width	40 mm
Height	80 mm
Length	2000 mm
Drill hole spacing	25 mm
Hole diameter	4.5 mm ... 14 mm

Material specifications

Color	stone gray (RAL 7030)
Material	PVC
Flammability rating according to UL 94	V0
Components	Lead-free

Cable/line

Halogen-free	no
--------------	----

Mechanical properties

Usage cross-section	2671 mm ² (100 %)
Number of cables at 60% filling volume	96 (2.5 mm ² Ø 3.4 mm)

Technical data

Drill hole spacing	25 mm
--------------------	-------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
---------------------------------	------------------

CD 40X80 - Cable duct

3240198

<https://www.phoenixcontact.com/us/products/3240198>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240198>



CSA

Approval ID: 80202282



VDE approval of drawings

Approval ID: 40058456



UL Recognized

Approval ID: E328576

CD 40X80 - Cable duct

3240198

<https://www.phoenixcontact.com/us/products/3240198>



Classifications

ECLASS

ECLASS-13.0	27400703
ECLASS-15.0	27400703

ETIM

ETIM 9.0	EC000012
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

CD 40X80 - Cable duct

3240198

<https://www.phoenixcontact.com/us/products/3240198>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com