

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022013217

Status:

Obsolete

Overview:

kk

Description:

2.54mm (.100") Pitch KK® Crimp Terminal Housing, Friction Ramp, 21 Circuits, Use with 2759|6459|41572



image - Reference onlySeries

Documents:

Drawing (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	2695
Application	Signal
Overview	kk
Product Name	KK®
Physical	
Circuits (maximum)	21
Color - Resin	Natural (White)
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm (.100")
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	0°C to +75°C
Material Info	
Old Part Number	2695-21RP

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

2695Series

Mates With

2.54mm (.100") Pitch KK® PCB Headers
42375 , 42377 , 42376 , 4030 , 6373 , 6410

Use With

KK® Crimp Terminal 2759 , 6459 , 41572

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION