

Loading...

50ft Cat6 Snagless Unshielded (UTP) Ethernet Network Patch Cable - Pink

Snagless design for network adapters, hubs, switches, routers, DSL/cable modems, patch panels and other high performance networking applications.

★★★★★

5.0

1 Review

Roll over image to zoom in

Product # : 04060

Connector 1 : (1) RJ-45 Male

Connector 2 : (1) RJ-45 Male

Colors :

Pink

Red

Blue

Grey

+ show all colors

Lengths :

50ft

0.5ft

1ft

2ft

3ft

4ft

+ show all lengths

Out Of Stock, available on February 10th

1

Add

VISA

MasterCard

AMERICAN EXPRESS

DISCOVER

[print](#) [share](#) [chat](#)

- Description
- Features
- Specs
- Uses
- Support

Product Description

For fast Ethernet and Gigabit computer networks that require bandwidth-intensive voice, data, or video distribution applications. Meets all Cat6 TIA/EIA standards, and drastically reduces both impedance and structural return loss (SRL). Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point. Constructed from high quality copper cable, this design minimizes Near-End Crosstalk (NEXT) levels. The molded, snagless boot prevents unwanted cable snags during installation and provides extra strain relief. Available in a variety of colors to easily color-code your network installation.

Product Features

- Snagless design protects clips when plugging and unplugging
- Standard RJ45 connectors and unshielded twisted pair wires
- Available in 10 colors to color-code a network
- Available in lengths up to 150ft

 **WARNING:** Cancer and Reproductive Harm www.P65Warnings.ca.gov

Product Specifications

Color :	Pink
Length :	50.00 Foot
Jacket Rating :	Standard Non-Rated

UPC :	757120040606
Warranty :	Lifetime
Vendor :	C2G
Weight :	1.387 LB

Electrical Characteristics

- Conductor DC Resistance - 9.38Ω/100m (maximum)
- Impedance - 100Ω
- Capacitance - 5600pf/100m
- Propagation Delay - 545ns/100m (maximum)
- Delay Skew - 45ns/100m (maximum)

Physical Characteristics

- Wiring Scheme - T568B
- Standard: Category 6 TIA/EIA-568-B-2.1, draft 9
- Connector: 50 micron gold-plated RJ45
- Temperature Rating - 60°C
- Voltage Rating - 30V
- Approvals - RoHS Compliant
- Warranty - Lifetime
- Package Type - Polybag

Conductor (Qty. 4 twisted pair)

- Conductor Type - 24AWG (7/0.20), Stranded Bare Copper
- Insulation - H-D PE
- Diameter - 0.98 ± 0.05mm
- Colors - Blue, Blue-White, Orange, Orange-White, Green, Green-White, Brown, Brown-White

Connector Type (Qty. 2)

- Connector Type - 8P8C (RJ45)
- Gender - Male
- Connector Material - Polycarbonate
- Contact Material - Copper Alloy, Gold Plating - 50µm
- Hood Material - Molded PVC

Overall Cable

- Jacket - PVC
- Minimum Average Thickness - 0.60mm
- Outer Diameter - 6.20 ± 0.30mm

Product Uses

- Gigabit 1000 BASE-T; 100 BASE-T; 10 BASE-T (IEEE 802.3)
- 4/16 Mbps Token Ring (IEEE 802.5); 100 VG-AnyLAN
- 100 Mbps TP-PMD (ANSI X3T9.5); 55/155 Mbps ATM
- Voice; T1

Product Support

Downloads

- Download the [technical specifications](#)

Info

[About Us](#)

[Order History](#)

[Where To Buy](#)

[More](#) ▾

Service

[Contact Us](#)

[OEM Solutions](#)

[Tech Support](#)

[More](#) ▾

Resources

[Connector Guides](#)

[ConnectXpress](#)

[Drivers & Manuals](#)

[More](#) ▾

Have A Question?

Get help with [Chat](#)

Call C2G **800.506.9607**



United States | [Europe](#) +

Copyright © 2019 C2G. All Rights Reserved

