

BU-116K-@
(Industrial Grade Kelvin Battery Clip)



- The BU-116K is a PE-coated Kelvin battery clip (jaws electrically isolated). Can be connected up to 8 AWG wire via solder connection. Designed to accommodate a strain relief (Heyco 3254 or equivalent, not included).
- Overall length 6.3" (160mm), overall width 1.1" (28mm), overall height 3.4" (86mm), jaws open to maximum of 2.0" (51mm)
- Material: Handles PE-coated steel
 Jaws Nickel-plated solid copper
- Rating: Current 100 Amps
- Color: The "@" in the model number indicates color.
 Available colors are: -0 Black, -2 Red
- RoHS 3 compliant