

 PRODUCTS ▾

 DISTRIBUTOR INVENTORY

 INDUSTRIES ▾

 SUPPORT ▾

 NEWS & EVENTS ▾

 ABOUT US ▾

3100U 00031440

Products > Sensors > Humidity, Thermal & Flexible Heater Products > Thermostats/Thermal Switches > Precision > Preconfigured Redi-Temp > 3100U Series > **3100U 00031440**

Overview

3100 Series Hermetic Thermostats.

The 3100 Series consists of a single pole, single throw switch activated by a snap-action bimetal disc. Temperature c



[View More](#)

 view all 3100U 00031440 literature

 view distributor inventory

 sample request

 email support

 get support

 email sales

 find a distributor

 email this page

Technical Specifications

Functional Properties	Open on rise	Reset Type	Automatic
Operating Temperature	-29 °C to 260 °C [-20 °F to 500 °F]	Amperage	3 A resistive max.
Voltage	120 Vac	Open Temperature	54.4 °C [130 °F]
Open Tolerance	2.8 °C [5 °F]	Close Temperature	43.3 °C [110 °F]
Close Tolerance	2.8 °C [5 °F]	Environmental Exposure Range	-62 °C to 288 °C [-80 °F to 550 °F]

[View More](#)

View documents in: English 

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
 Precision and High Reliability Thermostats	Datasheet	--	4MB
 Thermostats Line Guide	Product Line Guide	English	444KB
 Thermal Sensors	Product Range Guide	English	2MB

Product Features

- Hermetically sealed
- Tight tolerances
- Tight differentials

Applications

- Computers
- Medical electronics
- Power supplies
- Industrial controls
- Test equipment
- Infotech

NAVIGATION LINKS

[HOME PAGE](#)
[PRODUCTS](#)
[DISTRIBUTOR INVENTORY](#)
[INDUSTRIES](#)
[SUPPORT](#)
[NEWS & EVENTS](#)
[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)
[LEARN CENTER](#)
[REQUEST ACCESS TO ECOM](#)
[SALES/AD PORTAL LOGIN](#)
[SALES/AD PORTAL ACCESS REQUEST](#)
[SAMPLE REQUEST](#)
[SUPPLIER MICROSITE](#)

LANGUAGE

[English](#) 

SOCIAL MEDIA**SITE INFORMATION**

[PRIVACY STATEMENT](#)
[SITEMAP](#)

[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.