

Product Line

- Single Pair Ethernet >
- ZConnect >
- Ceres >
- Accessory
- Large Size
- Macro Size
- Middle Size
- Mini Size
- Others (GBD)
- Others (MAB)
- Others (PLD)
- Standard Size
- X-Lok >
- M Series >
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >



BD-08AFFM-SR7A04

Operating Temperature: -20°C ~ +80°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: PVC

Certificate: N/A

You must login first for view the price

Quantity

- 1 +

Add to Cart

Inquiry

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

Ceres. Standard...
1BD-08PMMS-SC7001
-40°C ~ +105°C

Ceres. Standard...
ABD-08PMMS-SC7001
-40°C ~ +105°C

Ceres. Standard...
BD-08PMMM-SL7A01
-20°C ~ +80°C

Ceres. Standard...
BD-08PMMM-SL7A02
-20°C ~ +80°C

ABOUT AMPHENOL LTW

SUPPORT

PARTNERS


DOWNLOAD CENTER

FEEDBACK

- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >

Add to Cart

Inquiry

Specifications		Download / CAD	
Nominal Current		Connector Type	
5A		Overmolded	
Shielded		No. of Contacts	
Plastic, Non-shielded		08	
Connector Gender		Backshell	
Female		Right Angle	
Mating Style		IP Rating	
Screw Thread		IPX7	
Assembly Style			
N/A			
<div> More Options</div>			

People Also Bought

