

Specifications

Photo is representative

Eaton DR73-821-R

Eaton DR inductor, 820 uH, 0.27 A Irms, 0.28 A ISAT, 4600 mΩ resistance, SMT mounting, Ferrite, 2-pins, 1350 qty.

General specifications

PRODUCT NAME	Eaton DR73 inductor
CATALOG NUMBER	DR73-821-R
UPC	051712888837
EAN	5027590169110
PRODUCT LENGTH/DEPTH	7.6 mm
PRODUCT HEIGHT	3.55 mm
PRODUCT WIDTH	7.6 mm
PRODUCT WEIGHT	0.609 g
COMPLIANCES	RoHS Compliant

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	0.27 A
ISAT	0.28 A
PACKAGE QUANTITY	1350
MATERIAL	Ferrite
AUTOMOTIVE GRADE	No
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	4600 mΩ
TERMINALS	7.5x7.5x3.35mm
SERIES	DR73

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton DR high power density high efficiency shielded drum core power inductors data sheet](#)

[Eaton Specification Sheet - DR73-821-R](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

