

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

JUN , 2005.

© COPYRIGHT 2005 BY TYCO ELECTRONICS CORPORATION.

ALL INTERNATIONAL RIGHTS RESERVED.

LOC

DIS

REVISIONS

变更

DESCRIPTION

DATE

DWN

APVD

	F
--	---

LTR






F1

REVISÉD

200CT2010

0	K	M
---	---	---

F T



① MATERIAL;
HOUSING: HIGH TEMPERATURE THERMO PLASTIC
UL94V-0, COLOR; BLACK
CONTACT: COPPER ALLOY

② FINISH;
CONTACT AREA: GOLD PL. 0.76 μ m MIN OVER NICKEL PL.
COMPLIANT PIN ACTION AREA: 0.5 μ m MIN MATTE TIN
OVER NICKEL PL.

③ NOT SPECIFY BY PCI EXPRESS STANDARD

⑤ FINISH;
CONTACT AREA: GOLD PL. 0.76 μ m MIN OVER NICKEL PL.
COMPLIANT PIN ACTION AREA: 0.5 μ m MIN BRIGHT TIN-LEAD
OVER NICKEL PL.

⑫ FINISH;
CONTACT AREA: GOLD PL. 0.38 μ m MIN OVER NICKEL PL.
COMPLIANT PIN ACTION AREA: 0.5 μ m MIN MATTE TIN
OVER NICKEL PL.

13 CONNECTOR HAS MET THE REQUIREMENTS PER
PCI EXPRESS GEN 2 TECHNICAL DOCUMENT.

△ ₃	△ ₂	PRODUCING	70	↑	73.15	89	71.65	164	16	5-	↑	-4
	↑	PRODUCING	70		73.15	89	71.65	164	16	3-		-4
	△ ₅	PRODUCING	37		40.15	56	38.65	98	8	3-		-3
	↑	PRODUCING	128		131.15	147	129.65	280	/	1-		-5
		PRODUCING	70		73.15	89	71.65	164	16	1-		-4
△ ₃		PRODUCING	37	3.25	40.15	56	38.65	98	8	1-1871058		-3
		PRODUCING	20	↑	23.15	39	21.65	64	4	1-	↑	-2
		PRODUCING	6	3.25	9.15	25	7.65	36	1	1-		-1
		PRODUCING	128	↑	131.15	147	129.65	280	/			-5
		PRODUCING	70		73.15	89	71.65	164	16			-4
		PRODUCING	37	2.0	40.15	56	38.65	98	8	1871058		-3
		PRODUCING	20	↑	23.15	39	21.65	64	4		↑	-2
	△ ₂	PRODUCING	6	2.0	9.15	25	7.65	36	1	1871058		-1
FINISH	TOOLING STATUS	N	D	C	B	A	POS.	PORT	P/N			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	02DEC05
T.KATANO	

CHK	02DEC05
R.MURAYAMA	

APVD	02DEC05
K.KODAIRA	

PRODUCT SPEC		
製品規格	108	78310

108-78340

APPLICATION SPEC

取付適用規格

WEIGHT

 Tyco Electronics	Tyco Electronics Corporation Kawasaki, Japan
---	---


NAME 名称	PCI EXPRESS CARD EDGE CONN. WITH COMPLIANT PIN V-TYPE
------------	--

NOT the LATEST

SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
------	-----------	------------------	---------------

A3 00779	C=1871058	
----------	-----------	---

1470-19 (1/08)



MODULE LAYOUT(MATING PART ONLY)

NOT SPECIFY BY PCI EXPRESS STANDARD	A1,B17,B31,B48,B81,B139	130.15	131.15	147	128	280	
	A1,B17,B31,B48,B81	72.15	73.15	89	70	164	16
	A1,B17,B31,B48	39.15	40.15	56	37	98	8
	A1,B17,B31	22.15	23.15	39	20	64	4
	A1,B17	8.15	9.15	25	6	36	1
	PRSNT PIN	E	C	B	N	POS.	PORT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 耗
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0-PLC ± ±0.13
1-PLC ± ±1
2-PLC ± ±
3-PLC ± ±
4-PLC ± ±
ANGLES ±
FINISH
仕上

DWN
CHK
APVD
PRODUCT SPEC
製品規格
APPLICATION SPEC
取付適用規格
WEIGHT
CUSTOMER DRAWING

Tyco Electronics
Tyco Electronics Corporation
Kawasaki, Japan

NAME
名称
PCI EXPRESS CARD EDGE CONN.
WITH COMPLIANT PIN V-TYPE

SIZE
A3
CAGE CODE
00779
DRAWING NO
番号
C-1871058
RESTRICTED TO

SCALE
尺度
8:1
SHEET
2 of 2
REV
E1

1470-19 (1/08)

Downloaded from Arrow.com