

Specification Sheet

Part Number: 151-00994

The 90-degree configuration of this mini channel creates a solution for routing a wire harness around a corner.

Design allows the mini channel to be used with a wide range of panel thicknesses and hole diameters.



Disc prevents rattling in high-vibration applications and protects against leakage and debris.

Mini Channel, 1.2" Long, 90° Angle, Arrowhead, PA66HIRHSUV, Black, 4000/ctn

Article Number 151-00994

Type BC90AH

Color Black (BK)

Quantity Per pack

Product Description HellermannTyton's Bundling Clips create a solution that allows the harness to be routed around a corner, and fixated into the panel at this location.

Short Description Mini Channel, 1.2" Long, 90° Angle, Arrowhead, PA66HIRHSUV, Black, 4000/ctn

Global Part Name BC90AH-PA66HIRHSUV-BK

| | |
|---|---------------|
| Length L (Imperial) | 0.98 |
| Length L (Metric) | 25.0 |
| Fixation Method | Arrowhead |
| Width W (Imperial) | 0.06 |
| Width W (Metric) | 1.5 |
| Height H (Imperial) | 0.98 |
| Height H (Metric) | 24.0 |
| Panel Thickness Min (Imperial) | 0.02 |
| Panel Thickness Max (Imperial) | 0.07 |
| Panel Thickness Min (Metric) | 0.5 |
| Panel Thickness Max (Metric) | 1.8 |
| Mounting Hole Diameter D (Imperial) | 0.24 - 0.27 " |
| Mounting Hole Diameter D (Metric) | 6.2 - 6.8 mm |
| Mounting Hole Diameter D Min (Imperial) | 0.24 |
| Mounting Hole Diameter D Max (Imperial) | 0.27 |
| Mounting Hole Diameter D Max (Metric) | 6.8 |

| | |
|--|--|
| Disc Diameter (Metric) | 21.34 |
| Disc Diameter (Imperial) | 0.84 |
| Material | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| Material Shortcut | PA66HIRHSUV |
| Flammability | UL 94 HB |
| UV Resistant (Yes/No) | Yes |
| Use Conditions | For Indoor and Outdoor Use |
| Operating Temperature | -40°F to +221°F (-40°C to +105°C) |
| Operating Temperature intermittent, 1000 hours | +320°F (+160°C) |
| Operating Temperature intermittent, 5000 hours | +257°F (+125°C) |
| Operating Temperature intermittent, 500 hours | +329°F (+165°C) |
| Reach Compliant (Article 33) | Yes |
| ROHS Compliant | Yes |
| Package Quantity (Imperial) | 4000 |

Package Quantity (Metric) 4000

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)