Part Number : 1300940523
Product Description : Support Grips for Fiber Optics, Closed Mesh, Single Eye, Bale Length 3", Cable Diameter 5.59-8.13mm (.220-.320"), Approximate Break Strength 136.08kg (300 lbs)
Series Number : 130094
Status : Active
Product Category : Cable Grips
Engineering Part Number : 36671



Documents and Resources

Drawings

1300940523_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130094
Description	Support Grips for Fiber Optics, Closed Mesh, Single Eye, Bale Length 3", Cable Diameter 5.59-8.13mm (.220-.320"), Approximate Break Strength 136.08kg (300 lbs)
Product Name	Fiber Optic
Type	Support Grip
UPC	78678836671

Agency

CSA	LR32159

Physical

Approximate Break Strength	136.08kg (300 lbs)
Bale Length	0.076m (3.00")
Body Style	Straight
Cable Diameter	5.59-8.13mm (.220-.320")
Color - Grommet	N/A
Eye Type	Single
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.064m (2.50")
Net Weight	1.000/g
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

Downloaded from Arrow.com.

Downloaded from Arrow.com.