

	1	2	3	4	5	6	7	8
A								
B								
C	27	33614311000003	FO breakout cable, MM, 2-channel, 62.5/125µm, PUR, black	100				
	26	33614310900003		90				
	25	33614310800003		80				
	24	33614310700003		70				
	23	33614310600003		60				
	22	33614310500003		50				
	21	33614310450003		45				
	20	33614310400003		40				
	19	33614310350003		35				
	18	33614310300003		30				
	17	33614310250003		25				
	16	33614310200003		20				
	15	33614310150003		15				
	14	33614310140003		14				
	13	33614310130003		13				
	12	33614310120003		12				
	11	33614310110003		11				
	10	33614310100003		10				
	9	33614310090003		9				
	8	33614310080003		8				
	7	33614310070003		7				
	6	33614310060003		6				
	5	33614310050003		5				
	4	33614310040003		4				
	3	33614310030003		3				
	2	33614310020003		2				
	1	33614310010003		1				
F	Cont. no.	Part no.	Type of cable	Dim. a[m]	 HARTING Customised Solutions D-32339 Espelkamp All rights reserved Department HCS - RO  All Dimensions in mm Tech. Character. Free size tol. According to production drawing Created by COSTEA Costea Inspected by 402676 Gross Standardisation MUNTEANV Muntean Date 2021-02-23 State Final Release Title FO CA PP2-LCdx, 62.5µ, OM1, PUR Doc-Key / ECM-Nr. 100677882/UGD/009/E 500000189720 Type TB Number 3361431XXX0003 Rev. E Page 2/2			