



OCEAN APPLICATORS



✓ Active

TE CONNECTIVITY (TE)
OC-AT-E-FM-080F110OV-040-0927
[AMP](#)

2150424-1
TE Internal Number: 2150424-1

[Not in Scope for EU RoHS/ELV Compliance](#)

Region **Worldwide**

Tool Type **Applicator**

Spare Parts Tooling **No**

Applicator Style **OCEAN - Atlantic**

Applicator Feed Style **End Feed**

Product Drawings

[Ocean End Feed Applicator](#)

PDF
English

Catalog Pages/Data Sheets

[4-1773460-5_New Series Of Applicators From](#)

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Tool Type	Applicator
Spare Parts Tooling	No
Applicator Style	OCEAN - Atlantic
Applicator Feed Style	End Feed
Applicator Feed Type	Mechanical

Product Availability

Region **Worldwide**

Product Compliance

[Statement of Compliance](#)
PDF

[VIEW ALL PRODUCT COMPLIANCE](#)

Relation Type

RELATIONSHIP

Spare Parts
Spare Parts

See All Spare Parts



PRODUCT - SPARE PARTS

Application Tooling - OCEAN Applicators
AMP

CRIMPER, INSULATION F
PREMIUM - 1633963-1

TE INTERNAL NUMBER: 1633963-1

✓ Active

Not in Scope for EU RoHS/ELV
Compliance

Region **Worldwide**

Tool Type **Applicator**

Spare Parts Tooling **Yes**

Spare Parts Tool Type **Crimper**

✓

RELATIONSHIP

Spare Parts
Spare Parts

See All Spare Parts



PRODUCT - SPARE PARTS

Application Tooling - OCEAN Applicators
AMP

Blade, Slug - 2217206-7

TE INTERNAL NUMBER: 2217206-7

✓ Active

Not in Scope for EU RoHS/ELV
Compliance

Region **Worldwide**

Tool Type **Applicator**

Spare Parts Tooling **Yes**

Spare Parts Tool Type **Shear**

✓

RELATIONSHIP

Spare Parts
Spare Parts

See All Spare Parts



PRODUCT - SPARE PARTS

Application Tooling - OCEAN Applicators
AMP

CRIMPER, WIRE .080 "F"
- 3-456405-7

TE INTERNAL NUMBER: 3-456405-7

✓ Active

Not in Scope for EU RoHS/ELV
Compliance

Region **Worldwide**

Tool Type **Applicator**

Spare Parts Tooling **Yes**

Spare Parts Tool Type **Crimper**

✓