

## Han 10B HTE M32 PFT CL



Image is for illustration purposes only. Please refer to product description.

Part number	19 30 010 1142
Specification	Han 10B HTE M32 PFT CL
HARTING eCatalogue	<a href="https://b2b.harting.com/19300101142">https://b2b.harting.com/19300101142</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> B
Type of hood/housing	Panel feed through housing
Type	High construction

### Version

Locking type	Central locking lever (on the hood)
Size	10 B
Version	Top entry
Cable entry	1x M32
Field of application	Standard hoods/housings for industrial connectors

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
RoHS	compliant
ELV status	compliant



Pushing Performance

## Material properties

China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

CE	Yes
----	-----

## Commercial data

Packaging size	1
Net weight	292.5 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors