



APPROVED: _____
 DATE: _____ TITLE: _____



Rev	AWO #	Description	Date	Appr
-		RELEASED	9/19/05	
A		REDRAWN	4/16/10	
B		ADDED DIM.	12/1/15	AY/YC
C		UPDATE DRAWING	12/24/20	OW/LX

D

D



RECOMMENDED PCB LAYOUT

**SPECIFICATIONS:****Material:**

Insulator: Nylon, rated UL 94V-0

Insulator color: Nature

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Voltage rating: 250V AC, DC

Current rating: 3A AC, DC

Insulation resistance: 1000 Mohms min

Dielectric withstanding voltage: 800 VAC for 1 minute

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant.



Positions: 02 thru 12

A= .098 [2.50] x No. of Space

B= .098 [2.50] x No. of Space + .197 [5.00]

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES HOLES
 .X ± .10 ØX ± .10
 .XX ± .020 ØXX ± .015
 .XXX ± .015 ØXXX ± .010

APPROVALS

DATE

DRAWN SS 9/19/05

CHECKED

APPROVED

ADAM
TECH

 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

 TITLE: 2.5MM SHROUDED HEADER, SINGLE ROW,
 TIN PLATED

25SH-C-XX-TS

REV. C

REF: S00016T

SCALE: NTS

SHEET 1 OF 1