


HONEYWELL
PART NUMBER

WA-2RQ1-D6

REV	DOCUMENT	CHANGED BY	CHECK
B	0048645	KNR 06FEB09	CMH



- NOTES
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000±.002 CENTERS
 - 2 HARDWARE FURNISHED UNASSEMBLED

CATALOG LISTING
WA-2RQ1-D6
ABM5000

REPLACES:
X201720 - WA

CHARACTERISTICS	ELECTRICAL DATA
OPERATING FORCE - - - - - 14 - 22 OZ	CONTACT ARRANGEMENT S P N C
RELEASE FORCE - - - - - 10 OZ MIN	L23 20A - 125, 250 OR 480 VAC 10A - 125 VAC "L" 1HP - 125 VAC, 2HP - 250 VAC 1/2A - 125 VDC, 1/4A - 250 VDC
DIFFERENTIAL TRAVEL - - - .002 - .0075	L288 L308 L315
OVERTRAVEL - - - - - .219 MIN	20(3)A 250V ~ T85 5E4

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:
NO PLACES X ± -
ONE PLACE .X ± .030
TWO PLACE .XX ± .015
THREE PLACE .XXX ± .005
ANGLES X ± -
THIRD ANGLE PROJECTION

DRAWN	SSK	30JAN09
CHECK	CMH	30JAN09
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

Honeywell					
TITLE SWITCH - BASIC					
SIZE	TYPE	CAGE CODE	DRAWING NAME	REV	
B	I	-	WA-2RQ1-D6	B	
SCALE	NONE	SHEET		I OF I	